



# HDMI EDID Detective Plus



EXT-HD-EDIDPN

## Keep HDMI sources and displays in perfect sync

High Definition displays with HDMI inputs use EDID (Extended Display Identification Data) to ensure that a connected Hi-Def source sends compatible audio and video signals. In some scenarios, this data can be lost, resulting in an incorrect signal or complete loss of audio and/or video. The Gefen HDMI EDID Detective Plus has been designed specifically to address this issue by recording the display EDID data and making it available to the Hi-Def source reliably and on a continuous basis. With DDC re-clocking technology, the reliability of HDCP handshaking is improved, ensuring that the Hi-Def source always receives the correct EDID. Using the Gefen Syner-G PC software or terminal emulation via USB, the installer can also manipulate/modify the EDID data to meet installation-specific requirements and resolve system-specific compatibility issues. The HDMI EDID Detective Plus has been designed for quick and easy programming and installation.

## How It Works

To program the EDID, connect the included HDMI cable from the Detective to the HDMI input of the display. Connect the included power supply to the unit and plug the power cord into an available electrical outlet. Disable the Write Protect Switch, set the DIP switches to the appropriate positions, and press the Program button. Once the EDID programming is completed, the display and power supply can be disconnected without losing the recorded EDID. If a suitable EDID cannot be recorded, there are six pre-programmed EDID profiles and six user-programmable EDID banks that can be used. Instructions for selecting one of the pre-programmed EDID profiles and for copying/uploading additional EDIDs are outlined in the user's manual.

Connect an HDMI cable, up to the recommended maximum cable length, from the Hi-Def source to the HDMI input on the Detective. Re-connect the included DC power supply and plug the power cord into an available electrical outlet. Power on the source and the display and a pristine Ultra High Definition picture will appear.

## Features\*

- Supports resolutions up to 1080p Full HD, and 1920 x 1200 (WUXGA)
- HDMI Features Supported:
  - HDCP
  - 12-bit Deep Color
  - LPCM 7.1 audio, Dolby® TrueHD, Dolby Digital® Plus, and DTS-HD® Master Audio™
  - 3DTV pass-through
  - Lip-Sync pass-through
  - CEC pass-through
- USB port for advanced programming of features such as EDID management.
- Configurable EDID using Gefen Syner-G™ software suite, downloadable from Gefen website.
- DDC Re-clocking
- Records the EDID from a display
- 6 pre-programmed EDID profiles
- 6 user-programmable EDID banks for copying/uploading EDIDs
- Selectable HDCP pass-through
- Field updatable firmware via USB port
- Compact and portable

## Specifications\*

- Maximum Pixel Clock: Up to 225 MHz\*\*
- Maximum TMDS Clock: Up to 225 MHz\*\*
- Video Input Connector: (1) HDMI Type A 19-pin, female, locking
- Video Output Connector: (1) HDMI Type A 19-pin, female, locking
- USB port: (1) Mini-B
- EDID Memory Size: 256 Bytes
- EDID Write Protect Switch: (1) slide-type
- EDID Program Button: (1) tact-type
- EDID programming switches: (3) DIP-type
- HDCP pass-thru/block switch: (1) DIP-type
- Power Supply : 5V DC
- Power Consumption: 5W (max.)
- Dimensions (W x H x D): 2.7" x 1.3" x 1.8" (68mm x 33mm x 46mm)
- Shipping Weight: 2 lbs (0.9kg)

\*\* Pass-through. Actual performance depends on cable length and quality.



Gefen, LLC  
20600 Nordhoff Street, Chatsworth CA 91311  
Tel. (818) 772-9100 (800) 545-6900 Fax (818) 772-9120  
www.gefen.com

\* Features and specifications are subject to change without notice.  
All trademarks are properties of their respective owners.  
Copyright © 2013 Gefen LLC.